



250
LUMEN



35H
RUNTIME



21M
RANGE



IP65/IK07
IP RATING

NEW PB-7800 - INDUSTRIAL MAGNETIC POWER BANK WITH FLASHLIGHT

- High quality 3.7v 7800mAh li-ion battery
- Intelligent multiple outputs - 5V 2.4A / 9V 2A / 12V 1.5A
- Faster 2A USB-C charging - 5 hour charge time
- Over-charge, over-load, deep-discharge and short-circuit protection
- Battery level and charging indicators
- 250 Lumen 6500k SMD LED Flashlight
- Super tough nylon and TPR construction
- IK07 Shock proof - 2m drop proof
- IP65 Dust & water resistant
- Super strong magnetic base
- Sturdy rear metal pocket clip
- 1m high quality USB-C charging cable included

BATTERY	3.7v 7800mAh Li-ion Rechargeable Battery
WEIGHT	265g
DIMENSION	114 x 65 x 32mm



250 LUMEN FLASHLIGHT

USB
TYPE-C

