


EcoTank ET-M1100

DATASHEET / BROCHURE



Low cost business printing, high reliability, and minimal user intervention make this ink tank system printer perfect for home office printing.

With an extremely low TCO and three year warranty, this mono EcoTank printer for business features a stylish and compact design. Print up to an amazing 5,000 pages with the included ink supply, and the bottle allows for mess-free, easy refills. It has USB connectivity and a fast FPOT speed helps to keep productivity high.

Save money

A high ink yield with inkjet's low power consumption delivers a low TCO and a competitive cost per page.

Save time

Additionally, its high ink yields help deliver improved productivity. This reliable cartridge-free printer features an enhanced ink filling system and easy to use ink bottles, keeping intervention to a minimum. Thanks to the ink tank being positioned at the front of the printer showing a clear view of the ink levels, this new design is compact and allows easy access for refilling. Its fast First Page Out Time (FPOT) from sleep and 15ppm print speed mean you won't be waiting around for jobs.

Save energy

Inkjet technology helps keep energy levels low, without the need for any heat, unlike a laser, and of course, less energy use helps keep your energy bills low.

Business features

USB connectivity and a compact footprint mean that it's easy to place on a desktop and connect to a user's PC or laptop.

KEY FEATURES

- **Low TCO**
Keep your printing costs extremely low
- **High ink yields**
Print up to 5,000 pages with the included ink
- **Save time**
Fast FPOT
- **Low energy use**
Inkjet printing requires no heat
- **Easy to refill**
New bottles designed with no-spill

SUPPLIES

- EcoTank ET-MX1XX Series Black Bottle XL

C13T03M140 6,000 pages

LOGISTICS INFORMATION

SKU	C11CG95402BY
EAN code	8715946655369
Layer	5 Units

EcoTank ET-M1100

WHAT'S IN THE BOX

- Warranty document
- Setup guide
- CD Manual

INK YIELD DATA

T03M1

● 6,000 pages*

* Quoted yields are extrapolated based on Epson original methodology from the print simulation of Test Patterns provided in ISO/IEC 19752. 11,000 pages yield based on two ink bottles included with this printer. 6,000 pages yield based on EcoTank ET-MX1XX Series Black Bottle XL ink bottle sold separately. Quoted yields are NOT based on ISO/IEC24711. Quoted yields may vary depending on the images that you are printing, the paper type that you are using, the frequency of your prints and environmental conditions such as temperature.



PRECISIONCORE™

For more information please contact:

Telephone: 01952 607111 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740
+ Local call rate.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.

EPSON®