

# Gigaset A270A

Pure communication – with answering machine

- Integrated digital answering machine with up to 25 minutes of recording
- Handsfree mode at the handset
- Illuminated graphical display
- Long talk and standby time of up to 18 and 200 hours
- Telephone book for up to 80 entries
- Easy to operate keypad on base station (answering machine) and on handset
- Illuminated hands-free key



## Audio quality

- Handsfree mode at the handset
- Adjustable volume of handset sound (5 levels)
- Ringer melody output in handset and in base station via speaker
- Echo-mode for a better acoustic performance behind a router
- Advisory tone for key confirmation and low battery
- Hearing-aid-compatible

## Telephone book and dialling functions

- Telephone book for up to 80 names and numbers
- Name indication for: incoming calls, missed calls list, redial list
- Call preparation (input of phone numbers before the actual dialling procedure) with correction option
- Redial of the last 10 different numbers
- Programmable speed-dial shortcut keys (keys 2 – 9)
- Dialling procedure: Dual-tone multi-frequency dialling (DTMF), pulse dialling (DP)
- Dialling key (programmable flash times)

## Display

- Illuminated graphic display, 1,5" (diagonal), 34 x 22 mm (B x H), 1-line dot matrix with 14 characters + 1 line for icons + 1 line for soft keys
- Display illumination: amber
- In standby mode:
  - Display of date and time
  - Display of battery state of charge
  - Soft keys for fast selection of functions
  - Alarm clock symbol if an alarm time set
  - Number of registered handsets
- During a call: Display of call duration

## Call display and signalling

- Call display with telephone number or name (CLIP / CNIP)
- For incoming and missed calls
- Adjustable ringtones:
  - 10 melodies
  - 5 volume levels / OFF / crescendo
- Individual ringtones for external / internal calls

## Display of missed calls / caller list

- Missed calls are shown in the display
- List of the last 25 missed calls with number / name and time
- Direct dialling out of missed calls list via send button

## Keypad

- 12 numeric keys plus 5 function keys
- 2-way navigation key
- Key lock on/off via #-key (long press)
- Ringer tone on/off via \*-key
- Flash function (R) through long press on "0"-key
- Illuminated "pick up" and hands free key (green LED)

## Menu

- Convenient menu guidance in various languages (D, GB, F, I, E, P, TR, etc.)
- Easy operation via menu texts and soft keys

## Additional functions

- Plug-and-play - very easy installation: unpack, plug in, and call (handset registered ex works)

# Gigaset

Wherever you go.

- Alarm clock feature with adjustable melody
- Settings, telephone book, caller list, date and time functions are protected against power failure

## Features when operating multiple handsets

- Toll-free internal calling
- 2 calls possible at the same time (1 external and 1 internal between 2 handsets)
- Telephone book transfer between handsets
- Call forwarding to a different handset with dialling/call back function
- 3-way-conference (1 external and 2 internal parties)
- Call all or selected internal handsets
- Simultaneous ringing of all handsets for external calls

## Answering machine

- Integrated digital answering machine with up to 25 minutes recording
- Easy to use via handset and base station (illuminated play key and on/off key)
- 1 personal message recordable (approx. 170 seconds)
- 1 standard message pre-set (plug & play)
- Indication of new messages on handset and base station
- Recording time adjustable: unlimited, 1, 2, 3 minutes
- Call acceptance adjustable: immediately, after 10, 18, 30 seconds, automatic (toll saver)
- Announcement of date and time for each message by voice
- Call pick up function to answer calls during message recording
- Listen in on incoming message on base station and handset with takeover of call
- Recordings have unlimited protection against power failure
- PIN-protected remote control of answering machine

## ECO DECT

- Automatic reduction of the transmitting power depending on the distance between the handset and the base station
- Radiation-free in standby mode, even if several handsets are used, as long as all registered handsets support ECO DECT

## Technical Data

Configuration	<ul style="list-style-type: none"> <li>○ Connection of 1 external line (a/b)</li> <li>○ Up to 4 handsets can be registered (for more information also see <a href="http://www.gigaset.com/compatibility">www.gigaset.com/compatibility</a>)</li> <li>○ Transmission range expansion with Gigaset Repeater</li> </ul>
Interface	a/b (analogue)
Implementation	Main connection / telecommunication system
Standards	DECT, GAP
Handset	<ul style="list-style-type: none"> <li>○ Standby: up to 200 hours</li> <li>○ Talk time: up to 18 hours</li> <li>○ Batteries: 2 x AAA (NiMH)</li> <li>○ Range               <ul style="list-style-type: none"> <li>- in buildings: up to 50 m</li> <li>- outdoors: up to 300 m</li> </ul> </li> <li>○ Dimensions: 159 x 48 x 30 mm (H x W x D)</li> <li>○ Weight: 114 g (incl. batteries)</li> </ul>
Base station	<ul style="list-style-type: none"> <li>○ Power supply: 230 V plug-in power adapter</li> <li>○ Dimensions: 63x 128 x 103 mm (H x W x D)</li> <li>○ Weight: 134 g</li> <li>○ Base station suited for wall mounting</li> </ul>
Charger (for Duos/Trios only)	<ul style="list-style-type: none"> <li>○ Power supply: 230 V plug-in power adapter</li> <li>○ Dimensions: 75 x 69 x 38 mm (H x W x D)</li> <li>○ Weight: 34 g</li> <li>○ Charger suited for wall mounting</li> </ul>
Scope of supply	<ul style="list-style-type: none"> <li>○ 1 Base station Gigaset A270A</li> <li>○ 1 Handset Gigaset A270H</li> <li>○ 1 Plug in power adaptor</li> <li>○ 1 Telephone connection cable</li> <li>○ 2 AAA rechargeable batteries (NiMH)</li> <li>○ 1 Battery compartment cover</li> <li>○ 1 User manual</li> </ul>
Appliance colour	○ Black
Data sheet version	04.09.2017