



# SXA-815D

## ▶ SINGLE-ENDED CORDSETS



Euro-Style Quick Disconnect Cable

8 Pin Euro-Style Female Connector

5 m (15 ft) in Length

Non-Shielded

Part Number: 806308

## SPECIFICATIONS

<b>Number of Contacts</b>	8
<b>Number of Connectors</b>	1
<b>Cable Jacket Material</b>	PVC
<b>Cable Jacket Color</b>	Yellow
<b>Connector Body Material/Color</b>	PUR Black
<b>Outside Cable Diameter (mm)</b>	6
<b>Cordset Length (m)</b>	4.57
<b>Trunk Length (m)</b>	No Trunk
<b>Shield/No Shield</b>	No Shield
<b>Coupling Material/Color</b>	Nickel Plated Brass
<b>Maximum Temp. (°C)</b>	105

<b>Current Rating (A)</b>	2.0
<b>Minimum Temp. (°C)</b>	-40
<b>Voltage Rating (V)</b>	75 V ac/dc
<b>IP Rating</b>	IP67
<b>Primary Connector Type</b>	EURO
<b>Primary Coupling Method</b>	M12 Single Key
<b>Primary Gender</b>	Female
<b>Primary Orientation</b>	Straight
<b>Primary Number of Conductors</b>	8
<b>Primary AWG</b>	22
<b>Secondary Connector Type</b>	Flying Leads
<b>Feature: Hazardous Area</b>	No
<b>Oil/Grease Resistant</b>	No



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America