


## Data sheet | Item number: 762-4206/8000-001


Touch Panel 600; 54.6 cm (21.5"); 1920 x 1080 pixels; 2 x ETHERNET, 2 x USB, Audio; Visu Panel



[www.wago.com/762-4206/8000-001](http://www.wago.com/762-4206/8000-001)



RoHS  
Compliant



### Item description

PIO2 hardware configuration

- 2 x ETHERNET port for connecting to field devices and the engineering tool
- 2 x USB port for optional connection of a USB stick, mouse or keyboard
- Audio interface for connecting a headphone or loudspeaker

### Data

#### Technical data

Display diagonal	54.7 cm (21.5 Inches)
Display	Resistive touchscreen
Display colors	16.7 million colors
Graphics resolution	(1920 x 1080) px
Visualization	Webserver Web Visu
ETHERNET protocols	DHCP DNS FTP FTPS

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at 01788 568 008.



	HTTP HTTPS SSH
Communication	EtherNet/IP™ Adapter (Slave), library for e!RUNTIME (prerequisite: e!RUNTIME PLC 600 license) Modbus TCP Master/Slave (prerequisite: e!RUNTIME PLC 600 license) EtherCAT Master, requires an additional license and an existing e!RUNTIME PLC 600 license on the device
Operating system	Real-time Linux (with RT-Preempt patch)
Processor	ARM® Cortex™ A9
Programming environment	e!COCKPIT (based on CODESYS V3)
Main memory (RAM)	2,048 MB
Internal memory (flash)	4096 MB
Program memory	32 MB
Data memory	128 MB
Memory card type	microSD (max. 2 GB); microSDHC (max. 32 GB)
Indicators	five LEDs
Controls	Two brightness settings (High and Low) on the front
Supply voltage	SELV DC 24 V (18 ... 31.2 V); with reverse voltage protection

### Connection data

Connection technology: communication/fieldbus	Modbus TCP: 2 x RJ-45; 2 x USB 2.0 host (type A)
---	--

### Physical data

Width	554 mm / 21.811 inch
Height	358 mm / 14.094 inch
Depth	58 mm / 2.283 inch
Panel cutout (W x H)	(540 x 344) mm

### Mechanical data

Weight	5400 g
--------	--------

### Environmental requirements

Surrounding air temperature (operation)	0 ... 45 °C (in vertikaler Einbaulage; 0 ... +40 °C, abweichende Einbaulagen)
Surrounding air temperature (storage)	-20 ... 60 °C
Protection type	IP65

Subject to changes. Please also observe the further product documentation!



Note on protection type	IP65 (front side); IP20 (rear side), per EN 60529
Relative humidity (without condensation)	90 %
Mounting type	Clamping elements (included) or VESA mount (4 x M4x8)

### Commercial data






Packaging type	BOX
Country of origin	DE
GTIN	4055144002812
Customs tariff number	8471410000

### Compatible products

#### memory card

	<b>Item no.: 758-879/000-3102</b> Memory Card SD Micro; 2 GByte	<a href="http://www.wago.com/758-879/000-3102">www.wago.com/758-879/000-3102</a>
	<b>Item no.: 758-879/000-3108</b> Memory Card SD Micro; pSLC-NAND; 8 GB; Temperature range: -40 to 90°C	<a href="http://www.wago.com/758-879/000-3108">www.wago.com/758-879/000-3108</a>

#### software

	<b>Item no.: 2759-208/211-1000</b> Library MTP; Single License; Online activation	<a href="http://www.wago.com/2759-208/211-1000">www.wago.com/2759-208/211-1000</a>
	<b>Item no.: 2759-216/211-1000</b> e!RUNTIME; IEC 61131 runtime environment; 600; Single License; Online activation	<a href="http://www.wago.com/2759-216/211-1000">www.wago.com/2759-216/211-1000</a>
	<b>Item no.: 2759-2286/211-1000</b> e!RUNTIME; BACnet; 600; M; Single License; Online activation	<a href="http://www.wago.com/2759-2286/211-1000">www.wago.com/2759-2286/211-1000</a>
	<b>Item no.: 2759-266/211-1000</b> e!RUNTIME; EtherCAT Master; 600; Single License; Online activation	<a href="http://www.wago.com/2759-266/211-1000">www.wago.com/2759-266/211-1000</a>
	<b>Item no.: 2759-286/211-1000</b> e!RUNTIME; BACnet; 600; Single License; Online activation	<a href="http://www.wago.com/2759-286/211-1000">www.wago.com/2759-286/211-1000</a>

#### assembling

	<b>Item no.: 762-9001</b> e!DISPLAY7300T ; Clamping elements (4 pieces)	<a href="http://www.wago.com/762-9001">www.wago.com/762-9001</a>
--	--	--

Subject to changes. Please also observe the further product documentation!



## Downloads Documentation

### Manual

WAGO Touch Panel 600 Standard Line	1.5.0 01-Dec-2020	pdf 2.5 MB	Download
---------------------------------------	----------------------	---------------	----------

### Bid Text

762-4206/8000-001		xml 7.0 kB	Download
-------------------	--	---------------	----------

762-4206/8000-001		docx 20.3 kB	Download
-------------------	--	-----------------	----------

### System Description

Touch Panel 600, system description		pdf 727.2 kB	Download
-------------------------------------	--	-----------------	----------

## Installation Notes

## Product family

**Standard Line**  
[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at 01788 568 008.