



D26414

2000W Digital LED HEATGUN

Selling Proposition

- Durable hot air gun for Professional applications
- Excellent temperature control and memory setting for consistent temperature requirements
- 2000 Watt power with optimised cooling
- Compact and lightweight for easy handling and use

Standard Equipment

- Cone nozzle
- Fish tail surface nozzle

Warranty Specifications

- 1 Year Free Service Contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

| Specifications | |
|-----------------------------|----------------------|
| Power Input | 2000 Watts |
| Operating Temperature | 50-600 °C |
| Air Flow | 650 l/min |
| ´Gewicht | 0.85 kg |
| Länge | 265 mm |
| Height | 210 mm |
| Hand/Arm Vibration | 2.5 m/s ² |
| Uncertainty K 1 (Vibration) | 1.5 m/s ² |