

Product Specification PDF

Date	Correct as of 15th May 2019
Brand	C.K
Product	T5421
Description	MightyRod PRO Cable Rod Standard Set 10m
Barcode	5013969950649
Commodity code	8205598000
Country of origin	TW



Features & Benefits	~ Triple bonded steel connectors for extreme torsion and tensile strength □ glued, indented and crimped ~ 10 meters of 100% splinter-proof rods ~ 4 rod flexibilities for overhead, under floor, tight angled and obstructed runs ~ Super tough □MIGHTY-FIX□ zinc plated steel connectors □ tensile strength in excess of 275kg ~ Super flexible, low friction, Spira-FLEX rod for tight angled access points ~ Accessories: flexi lead (mini-flex), ring, hook, gender changer, flat bullet, domed bullet, in-line swivel ~ Total contents: 2 x 1m rods 7 mm Ø / 7 x 1m rods 6 mm Ø / 1 x Rod SpriaFlex 4 mm Ø / 1 x FlexiLead / 1 x Hook / 1 x Flat Bullet / 1 x Domed Bullet / 1 x Ring / 1 x Gender Changer / 1 x In-line Swivel
Applicable Standards	
Health & Safety	None applicable
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	20
Width mm	45	45	0	1320
Depth mm	45	45	0	230
Height mm	1300	1300	0	180
Weight	935	935	0	19.6
Packaging Information	Card use	0	0	Case
	Card gms	0	0	900
	Plastic use	0	0	-
	Plastic gms	0	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0