

J.17 | J - 3/8" METRIC 12-POINT SOCKETS




Norm :


NF ISO 2725-1, NF ISO 1711-1, ISO 2725-1, ISO 1711-1, DIN 3124, ASME B107.5

Description :

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.



Informations :

	J.17
A [mm]	17
d [mm]	21,7
d1 [mm]	23,4
L [mm]	30
L1 [mm]	13,0
12-Point [mm]	12
[g]	52