



Pushing Performance

Han CGM-M M40x1,5 D.19-28mm E.47



Part number	19 00 000 5078
Specification	Han CGM-M M40x1,5 D.19-28mm E.47
HARTING eCatalogue	https://b2b.harting.com/19000005078

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-M
Type of accessory	Cable gland

Technical characteristics

Wrench size	43 40
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M40
Clamping range	19 ... 28 mm

Material properties

Material (seal)	NBR
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Country of origin	Germany



Pushing Performance

Commercial data

European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)