



RECESSED LINEAR LIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 604 - 1410 940

[View more details](#)

TECHNICAL INFORMATION

Watts:	40
Lumens:	3200
Input Power:	AC:200-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Aluminium Alloy
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	120°
Color:	6400K
Dimension:	1200x70x60mm
Linkable:	Upto 12 Meters



FEATURES

- Recessed linear lights with a long lifespan of 30,000 hours
- Robust Aluminium body
- Linkable up to 12 meters using connectors
- Multiple connector options (Connectors not included)
- Excellent heat dissipation
- Suitable for commercial and residential applications

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 2.135
Unit CBM: 0.00599625
Dimension: 1200x70x60mm

MASTER BOX PACKAGING

Box Qty: 9
Qty Per Pallet: 126
Length (Box) mm: 75
Width (Box) mm: 65
Height (Box) mm: 1230

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157639897