



PRO EXIT LIGHTS SURFACE 12 HOURS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 836 - 1271 2938

[View more details](#)

TECHNICAL INFORMATION

Watts:	2
Lumens:	140
Input Power:	AC:220-240V, 50/60Hz
Body Type:	PC
LED Chip Type:	SMD-Samsung Chip
Dimmable:	No
Color:	6000K
Dimension:	380x51x195mm
Battery Type:	Ni-Cd 3.6V, 900mAh
Charging Time:	12 hours
Working Time:	>3 Hours
Battery Charging Current:	100-140mA
Battery Discharge Current:	200-280mA
Emergency Operation Time:	>3 Hours
No. Of Led:	16
LED Chip Solution:	12V 60mA

EXIT LIGHT Surface

Surface Installation



FEATURES

- Fitted with high efficiency Samsung LED Chips
- High-performance Ni-Cd batteries made for Longevity & low maintenance
- Low energy consumption only 2 watts
- Viewing distance of 24 meters both sides
- Green light indicator test button
- 3 ways different legends available
- Reliable Emergency backup of 3 hours
- Maintained operation
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

PACKAGING

Gross Weight (Kgs): 1.1
Unit CBM: 0.003693375
Dimension: 380x51x195mm

MASTER BOX PACKAGING

Box Qty: 10
Qty Per Pallet: 300
Length (Box) mm: 45
Width (Box) mm: 335
Height (Box) mm: 245

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157641357

CE/EMC

CE/LVD

