



### TECHNICAL INFORMATION

Watts:	200
Lumens:	28000
Input Power:	AC:90-300V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	Black
Body Type:	Diecast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>70
Operation Temperature:	-20°C to +45°C
Dimmable:	Yes
Beam Angle:	120°
Color:	4000K
Dimension:	260x145mm
lumens per watt:	140
LED Chip Solution:	9V 100mA

### PRO UFO SERIES MW 120° | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 58011 - 936 938

[View more details](#)



IP65  
RATING



5 YEAR  
WARRANTY



IK 07



Mean Well  
Your Reliable Power Partner



1-10V  
DIMMABLE



140  
Lumen/W

### FEATURES

- Powerful LED light source with lumen efficiency of 140 LM/W
- Radiator integrated cooling fins for efficient heat dissipation
- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- Designed with Meanwell driver
- Suitable for industrial usage, warehouses, supermarkets, workshops, factories, warehouses, highways, toll stations, gas stations, malls, exhibition halls, and stadiums

CE/EMC

CE/LVD



### PACKAGING

Gross Weight (Kgs): 4.4  
Unit CBM: 0.019968  
Dimension: 260x145mm

### MASTER BOX PACKAGING

Box Qty: 1  
Qty Per Pallet: 58  
Length (Box) mm: 200  
Width (Box) mm: 450  
Height (Box) mm: 450

### LISTING DETAILS

Commodity Code: 9405403990  
EanCode: 3800157655484