

# TIME LED®


## GALLERY 3W LED UNDER CABINET SPOTLIGHT

### SPECIFICATION SHEET

PRODUCT CODE: 780893, 780909, 780916

#### PRODUCT COLOUR

780893	Brushed Chrome
780909	Chrome
780916	White





#### SPECIFICATION

Product code	780893, 780909, 780916
Fitting	Under Cabinet Spotlight
Bulb shape	SMD
Wattage	3W
Equivalent wattage	24W
Lumens	90lm
Driver included	Yes
Cable Length	15cm
Cable Colour	White
Dimmable	No
Beam Angle	120°
Diameter	Ø75mm
Height	27mm
Weight	0.141kg
Lifespan	15,000 Hours
Warranty	2 Years
Energy consumption	3kWh/1000h
Input frequency	50Hz
Energy rating	A
Material	Iron
Packaging	White Box + Colour Sticker
IP Rating	IP20

#### OPTICAL TEST PARAMETERS

Voltage	220-240V
Current: 780909	0.023A
Current: 780893 and 780916	0.024A
Power: 780909	3.02W
Power: 780893 and 780916	3.01W
CCT	No
Ra	80
Lumens	284lm
Lumens per watt	90lm/W
Colour tolerance	<6
Power factor	0.5
Hertz	50/60Hz



TIME LED is part of Pitacs Limited

Bradbourne Point, Bradbourne Drive, Tilbrook, Milton Keynes, Buckinghamshire MK7 8AT

T: +44 (0)1908 271155 F: +44 (0)1908 640017 E: info@timeled.co.uk W: www.timeled.co.uk



SPEC\_780893\_780909\_780916\_V1\_JULY2020