

PRODUCT DATASHEET

DP HOUSING 1200 2x Lamp IP65

DAMP PROOF HOUSING | Damp-proof luminaire for T8 LED lamps



PRODUCT BENEFITS

- Prewired for easy installation of tubular AC LED lamps
- Robust housing
- Easy and quick installation
- 5 years guarantee

PRODUCT FEATURES

- Luminaire housing, available for 1 or 2 T8 LED lamps
- Type of protection: IP65
- Suitable for SubstiTUBE EM/UN and SubstiTUBE Connected



TECHNICAL DATA

Electrical data

Nominal voltage	220...240 V
Mains frequency	50/60 Hz

Light technical data

Beam angle	105.00 °
------------	----------

Dimensions & weight



Length	1261 mm
Width	103.0 mm
Height	75.0 mm
Product weight	1300.00 g

Colors & materials

Body material	Polycarbonate (PC)
Product color	Gray
Housing color	Gray
Cover material	Polycarbonate (PC)

Temperatures & operating conditions

Ambient temperature range	-30...+45 °C
---------------------------	--------------

Additional product data

Mounting type	Surface
Mounting location	Ceiling
Equipped with lamp	No

Capabilities

Dimmable	No
----------	----

Type of connection	Screw terminal
Holder designation	G13

Certificates & standards

Protection class IK (shock resistance)	IK08
Protection class	I
Type of protection	IP65
Luminaire with limited surface temperature, class "D"	No
Standards	CE/TÜV Rheinland/EAC/RoHS

Logistical data

Temperature range at storage	-20...80 °C
------------------------------	-------------

EQUIPMENT / ACCESSORIES

- All required accessories included

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075312456	Folding carton box 1	77 mm x 110 mm x 1265 mm	1478.00 g	10.71 dm ³
4058075312463	Shipping carton box 6	1280 mm x 231 mm x 245 mm	10141.00 g	72.44 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

- ▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.