

TECHNICAL DATA

Model Number: MC090D050U/F+
Type Single--Voltage AC/DC Adaptor

Electrical Data

Input	Input Voltage/Frequency	230V/50Hz
	Input Power	11.2W
Output	Rated Output Voltage	9V
	Rated Output Load Current	500mA
	Rated Output Power	4.5 VA
Resistance	Insulation Resistance	100MΩ(measured with 500V DC voltage)
Protection	Thermal Protection	Thermal fuse:125□/2A
	Withstand Voltage (Hi-Pot)	AC 3750V 50Hz for 1minute or AC4000V 2seconds

Mechanical Data

Supply Connection Type	SCHUKO type DIN49 MWST-1 464/F
Primary Turns & Wire Gauge	2050T/0.11mm
Secondary Turns & Wire Gauge	94T/0.45mm
Core Size	41mm×26mm
Output Plug Dimensions	5.0X2.5X12mm
Polarity	CENTRE POSITIVE
Unit Weight	230g
Dimensions	67×50×80(mm)