



CC-BC 15 M Battery Charger

Item No.: 1002261

Ident No.: 11016

Bar Code: 4006825614312

The Einhell CC-BC 15 M Battery Charger is an intelligent, micro-processor controlled system with multi-stage charging cycle. It is suitable for all standard 6V/12V vehicle batteries. The trickle charge function does not harm the battery being charged and prolongs battery life, particularly on seasonal vehicles. Over-discharged batteries can be restored with the rescue function. Over-charge, short circuit and reverse polarity protection prevent damage to the charger. The unit also comes with fully insulated terminal clamps. The LED battery voltage and charge status display show at a glance the current state of the battery.

Features

- Intelligent battery charger with microprocessor controller
- Multi-step charging cycle, contr. and monitored by microprocessor
- Universal battery charger for various battery types such as:
 - Gel, AGM, zero and low maintenance lead-acid batteries, etc...
- Automatic battery voltage adjustment for 6/12V vehicles
- Jump starting current: 100 A
- Trickle charge function for a continuously ideal charge status
- Optimal for season.vehicles with long idle times(convert./m-bike)
- Use will extend the life of the battery
- LED battery voltage and charging progress display
- Electr. protec. against overcharging, short-circuit&swapped poles
- Rescue function for exhausted batteries
- Totally insulated battery terminals



Technical Data

- Mains supply 220-240 V | 50 Hz
- Charging voltage 6 V/ 12V
- Suitable for batteries (from min. Ah to max. Ah): 3-300 Ah
- Boost engine output (Ampere for seconds) 100 A - 5 sec
- Charging current Min. (arith./eff.) - Max. 2 / [-] A (arith./eff.) on 6 V d.c.
- Charging current Min. (arith./eff.) - Max. 2 / [-] - 15 / [-] A (arith./eff.) on 12 V d.c.

Logistic Data

- Product weight 8.16 kg
- Gross weight single packaging 8.79 kg
- Dimensions single packaging 319 x 327 x 208 mm
- Pieces per export carton 2 Pieces
- Gross weight export carton 18 kg
- Dimensions export carton 340 x 320 x 415 mm
- Container quantity (20"/40"/40"HC) 1240 | 2300 | 3000

