

# A-2120DD-EB

The A-2120DD-EB is a high cost-performance mixer power amplifier suited for broadcasting paging or background music in schools, offices, shops, factories, mosques, churches and large rooms.



Article number A-2120DD-EB 1CE  
Alternative products: A-2120D-EB

## Specifications

|                          |   |
|--------------------------|---|
| Power source             | 220 - 240 V AC, 50 / 60 Hz  |
| Rated output             | 120 W   |
| Frequency response       | 50 Hz - 20 kHz ( $\pm 3$ dB)  |
| Distortion               | < 1 % (at 1 kHz, 1/3 rated output power)  |
| S/N ratio                | 60 dB (or more)   |
| Number of channels       | 1   |
| Connectable microphones  | 3   |
| Inputs                   | MIC 1: -60dBV, 600 Ohm, balanced, 5-pin DIN equivalent, phantom power selectable, + 21V<br>Mic 2-3: -60dBV, 600 Ohm, balanced, phone jack<br>AUX 1-2: -20 dBV, 10 kOhm, unbalanced RCA pin jack |
| Control input            | Mute: via DIN jack  |
| Outputs                  | Speaker: balanced (floating) / Rec out: 0 dBV, 600 $\Omega$ , unbalanced, RCA Pin Jack  |
| Dimensions (W x H x D)   | 420 x 100,6 x 280,3 mm  |
| Dimensions ( $\phi$ x D) | x 280,3 mm  |
| Finish                   | ABS resin, Steel plate, black,  |



# A-2120DD-EB

---

Appearance