



Quality Products. Service Excellence.

C4 Doors *C4DF Series*

Exclusively for use with the C4 Cabinet Series



Features

- Constructed in 16-gauge steel.
- Easily installs into **C4 Series** cabinets using integrated spring pin at top and bottom of door.
- Hinged on left, swings from right to left.
 - Need hinging on right? Order the **C4RHINGE**.
- Includes formed plastic handle, quarter-turn lock and hinges to mount on cabinet.
- Available in Solid, Louvered, Perforated, Window and Vented Window options.
- Finished in rugged textured black powder paint.



Accessories

- Cabinet Door Replacement Lock



Part No.	Part No.	Part No.	Part No.	Use with Cabinet	
				Rack Units	Width
Solid Door	Acrylic Door	Perforated	Perforated Split Doors		
C4DF2442SBK1	C4DF2442PBK1	C4DF2442VBK1	C4BD2442VBK1	24U	24.00
C4DF2473SBK1	C4DF2473PBK1	C4DF2473VBK1	C4BD2473VBK1	42U	24.00
C4DF2477SBK1	C4DF2477PBK1	C4DF2477VBK1	C4BD2477VBK1	44U	24.00
C4DF3077SBK1	C4DF3077PBK1	C4DF3077VBK1	C4BD3077VBK1	44U	30.00

*Perforated doors for both front and back of the cabinet are suggested for most server applications.

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.