


Part Number: 1951X13X

Type	Size	Rating	Description
LED	M8	130Vac	LED Prominent Panel Indicator

Dimensions (mm)



Part #	Colour	Current (mA)	Intensity (mcd)
1951X130	Red	5	36
1951X131	Green	5	10
1951X132	Yellow	5	15

Bezel types - X=0 satin chrome / X=1 black chrome / X=2 matt chrome

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Due to component tolerances, colour temperature variations may be observed
- 5 The terminals are not qualified for soldering
- 6 Sealed to IP67 above panel when supplied gasket used
- 7 The plastic(polycarbonate) has limited chemical resistance
- 8 RoHS & REACH SVHC compliant