


Part Number: 18626X3XX

Type	Size	Rating	Description
LED	T10	AC	10mm BA9s/13 MegaStarLED



Part #	Voltage (AC)	Colour	Current (mA)	Intensity (mcd)
1862613W3A	130	White clear	6	3x1600
1862613W3DA	130	White diffuse	6	3x1000
1862623W3A	230	White clear	2	3x900
1862623W3DA	230	White diffuse	2	3x300

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Lamp base in accordance with BS EN 60061-1:BA9s
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 The plastic(polycarbonate) has limited chemical resistance
- 7 RoHS & REACH SVHC compliant