


Part Number: 1938X35XM

Type	Size	Rating	Description
LED	M16	24Vac/dc	Flat Bezel Panel Indicator



Part #	Colour	Current (mA)	Intensity (mcd)
1938X350M	Red	8/16	1500
1938X351M	Green	7/14	100
1938X352M	Yellow	8/16	1000
1938X355M	Bright Green	7/14	1200
1938X357M	Blue	7/14	350
1938X35WMA	White	6/13	2000

Notes:

- 1 X = Chrome Bezel finish. 0 = Satin, 1 = Black, 2 = Matt
- 2 Electrical & optical data are measured at an ambient temperature of 25°C
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Voltage tolerance ±10%
- 6 Due to component tolerances, colour temperature variations may be observed
- 7 The terminals are not qualified for soldering
- 8 Degree of protection IP67 when used with the supplied gasket
- 9 The plastic(polycarbonate) has limited chemical resistance
- 10 RoHS & REACH SVHC compliant