




7190-7191

Diagonal Cutters with Tapered Head
& ESD Safe Handle









PRODUCT DETAILS

- Supreme series Tapered Head cutting pliers
- ESD safe mono-material handles with return spring
- Micro-bevel & flush cut
- The cutting capacity given is for copper wire
- Suitable for cutting Cu
- High performance alloyed steel
- Polished finish
- Numerically controlled machine grinding guarantees edge angle accuracy & contact, increases the tools reliability & consistency
- Precision induction hardened edges 58-60 HRC
- Screw joint that minimizes friction & maximizes alignment of cutting edges
- CO standard handle shape in conductive material









PRODUCT ATTRIBUTES







Product: **7190**

	Tapered		S	A	108 mm
A	4.29 in	B	9 mm	B	0,35 in
C	9 mm	C	0.35 in	D	6 mm
D	0,24 inch	F	1 mm	F	0,04 in
	0.2-1.0 mm		0.00-0.04 in		Micro-Bevel®
	50 g	Ω	Dissipative		







Product: **7191**

	Tapered		S	A	108 mm
A	4.29 in	B	9 mm	B	0,35 in
C	9 mm	C	0.35 in	D	6 mm
D	0,24 inch	F	1 mm	F	0,04 in
	0.1-1.0 mm		0.00-0.04 in		Flush
	50 g	Ω	Dissipative		

Product: **7190 CO**

	Tapered		S	A	108 mm
A	4.29 in	B	9 mm	B	0,35 in
C	9 mm	C	0.35 in	D	6 mm
D	0,24 inch	F	1 mm	F	0,04 in
	0.2-1.0 mm		0.00-0.04 in		Micro-Bevel®
	50 g	Ω	Conductive		

Product: **7191 CO**

	Tapered		S	A	108 mm
A	4.29 in	B	9 mm	B	0,35 in
C	9 mm	C	0.35 in	D	6 mm
D	0,24 inch	F	1 mm	F	0,04 in
	0.1-1.0 mm		0.00-0.04 in		Flush
	50 g	Ω	Conductive		