



1150D

Precision Measuring Digital Callipers with LCD Screen



PRODUCT DETAILS

- Stainless steel
- Digital display with LCD screen
- Measures mm and inch range from 0 to 150 mm or 6" with an increment of 0.01 mm or 0.0005" respectively
- Accuracy ± 0.03 mm
- Resolution 0.01 mm
- Supplied in protective box
- Depth gauge including limit and peak measurements
- Automatic turn off
- Display with LCD screen
- SR44 battery 1.5 V, life span 10 months or 7000 hours in normal use

PRODUCT ATTRIBUTES

Product				
1150D	25 x 90 x 245 mm	235 mm	150 mm	320 g

Follow the Fish!

