

USB A/A Extension Cable (USB-A Right-Angle M to USB-A F), 10-in. (25.4 cm)

MODEL NUMBER: U005-10I



Highlights

- Modifies the cable connecting to a PC to 90 degrees
- 24k gold-plated connectors and gold-plated copper contacts
- 24 gauge power wires

System Requirements

- USB port and device

Package Includes

- USB 2.0 Gold Extension cable - USB "A" Right-Angle Male to USB "A" Female - 10"

Features

- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/24 AWG data lines
- Gold-plated connectors and gold-plated copper contacts provide superior conductivity
- Molded connectors with built-in strain relief ensure that the cable lasts a long time

Specifications

OVERVIEW	
UPC Code	037332117861
Technology	USB 2.0 (High Speed); USB
PHYSICAL	
Color	Black
Cable Length (ft.)	0.8
Cable Length (m)	0.3
Cable Length (in.)	10
Cable Length (cm)	25.40
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.03



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	0.06
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
STANDARDS & COMPLIANCE	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>