

W400LVe

Bright projection



- **Bright WXGA projector – 4000 ANSI lumens**
- **Easy connectivity – HDMI, VGA, USB power**
- **Clear, powerful audio - 10W speaker**
- **Lightweight and portable**

Project bright and vibrant presentations effortlessly any time of day in HD. Designed for meeting rooms and classrooms, the W400LVe boasts amazing colour, long lamp life and energy-saving features for a lower overall cost of ownership.

This projector is easy to connect to with multiple inputs, a built-in speaker and USB Power. Perfect for connecting HDMI dongles such as Google Chromecast or a laptop, PC or Blu-ray player for clear projected images with sound. Portable and lightweight projector can be installed or taken on the move for off-site meetings with the optional carry bag (sold separately).



Specifications

Display/image	
Display technology	DLP
Resolution	WXGA (1280x800)
Brightness	4,000 lumens
Contrast ratio	25,000:1
Native aspect ratio	16:10
Aspect ratio - compatible	4:3,16:9
Keystone correction - vertical	+/-40°
Horizontal scan rate	15.38 ~ 91.15Khz
Vertical scan rate	50 ~ 85(120 for 3D)Hz
Uniformity	75%
Screen size	0.82m ~ 7.61m (32.24" ~ 299.53") diagonal
Lamp info	
Light source type	Lamp
Lamp watts	203
Lamp life hours (up to)	6000 (Bright), 12000 (Dynamic), 10000 (Eco), 15000 (Eco+)
Optical	
Throw ratio	1.55:1 ~ 1.73:1
Projection distance (m)	1m - 12m
Zoom	1.1
Zoom type	Manual
Focal length (mm)	21.85 mm~24mm/0.86"~0.945"
Native offset	112%
Connectivity	
Connections	Inputs 1 x HDMI 1.4a 3D support, 1 x VGA (YPbPr/RGB), 1 x Composite video, 1 x Audio 3.5mm Outputs 1 x VGA, 1 x Audio 3.5mm, 1 x USB-A power 1A Control 1 x RS232
General	
Noise level (typical)	27dB
Noise level (max)	29dB
PC compatibility	FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4.43MHz SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p, 576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)
3D compatibility	Side-by-Side:1080i50 / 60, 720p50 / 60 Frame-pack: 1080p24, 720p50 / 60 Over-Under: 1080p24, 720p50 / 60
3D	Full 3D
Security	Security bar, Kensington Lock, Password protected interface
OSD / display languages	25 languages: Arabic, Czech, Danish, Dutch, English, Farsi, Finnish, French, German, Greek, Hungarian, Indonesian, Italian, Japanese, Norwegian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish, Vietnamese
Operating conditions	5°C~40°C/41°F~104°F, max altitude 3000M/9843ft, max humidity 85%
Remote control	Card style
Speaker count	1
Watts per speaker	10W
In the box	AC power cord Remote control Battery Basic user manual
Optional wireless models	HDCast Pro, QuickCast Bundle, QuickCast starter kit, WHD200
Power	
Power supply	100 ~ 240V, 50 ~ 60Hz
Power consumption (standby)	0.5W
Power consumption (min)	187W
Power consumption (max)	225W
Weight and dimensions	
Dimensions (W x D x H) mm	316 x 244 x 108
Gross weight	4.4 kg
Net weight	3 kg

