

Banner's Call for Parts creates a steady workflow and pinpoints critical issues. Learn more.

ABR72L9-RDE2

▶ ABR BARCODE SERIES




ABR Series Barcode Reader

Resolution: 1600x1200 px; Lens: 9 mm Autofocus;
Light: Red; Diffused


Ethernet & Serial Communications; 1D + 2D
Code

Part Number: 808839



SPECIFICATIONS

IP Rating	IP67
Autofocus	Yes
Device Type	Imager BCR
Primary Housing Material	Aluminum
Camera Housing Size (HxWxL mm)	43 x 54 x 95
Image Resolution	1600 x 1200 pixels
Lens (mm)	9
Light Color	Red
Code Type	1D, 2D
Imager Type	Grayscale

 Offline (Contact Us)

Feature: PC Interface	Yes
EtherNet/IP	Yes
Common Ethernet Protocol	No
Modbus/TCP	Yes
PCCC	No
PROFINET	No
RS-232	Yes
RS-422	Yes
FTP	Yes
USB	No

COMPATIBLE PRODUCTS

BRACKET

	<p>SMBABR7RA</p> <p>Replacement Bracket for ABR 7000 Series Right-Angle Bracket Zinc-Coated Steel</p>
--	--

DOUBLE-ENDED CORDSETS

	<p>MQDEC-1703SS-DB25</p> <p>Euro-Style to DB25 Shielded Cable 17 Pin Female Straight to DB25 Male 0.91 m (3 ft) Length Black, PVC, Nickel Plated Coupling Nut</p>
	<p>MQDEC-1706SS</p> <p>Euro-Style Double Ended Shielded Cable 17 Pin Female Straight to 17 Pin Male Straight 1.83 m (6 ft) Length Black, PVC, Nickel Plated Coupling Nut</p>

	<p>MQDEC-1715SS</p> <p>Euro-Style Double Ended Shielded Cable 17 Pin Female Straight to 17 Pin Male Straight 4.57 m (15 ft) Length Black, PVC, Nickel Plated Coupling Nut</p>
	<p>MQDEC-1730SS</p> <p>Euro-Style Double Ended Shielded Cable 17 Pin Female Straight to 17 Pin Male Straight 9.14 m (30 ft) Length Black, PVC, Nickel Plated Coupling Nut</p>
	<p>STP-M12D-406</p> <p>Euro-Style M12 D-Code to RJ45 Ethernet Cable 4 Pin Male Straight to RJ45 1.83 m (6 ft) Length Teal, PVC, Nickel Plated Coupling Nut</p>
	<p>STP-M12D-415</p> <p>Euro-Style M12 D-Code to RJ45 Ethernet Cable 4 Pin Male Straight to RJ45 4.57 m (15 ft) Length Teal, PVC, Nickel Plated Coupling Nut</p>
	<p>STP-M12D-430</p> <p>Euro-Style M12 D-Code to RJ45 Ethernet Cable 4 Pin Male Straight to RJ45 9.14 m (30 ft) Length Teal, PVC, Nickel Plated Coupling Nut</p>

SINGLE-ENDED CORDSETS

	<p>MQDC2S-1706</p> <p>Euro-Style Quick Disconnect Shielded Cable 17 Pin Straight Connector 1.83 m (6 ft) Length Black, PVC, Nickel Plated Coupling Nut</p>
	<p>MQDC2S-1715</p> <p>Euro-Style Quick Disconnect Shielded Cable 17 Pin Straight Connector 4.57 m (15 ft) Length Black, PVC, Nickel Plated Coupling Nut</p>

MQDC2S-1730

Euro-Style Quick Disconnect Shielded Cable
17 Pin Straight Connector
9.14 m (30 ft) Length
Black, PVC, Nickel Plated Coupling Nut

MISCELLANEOUS**TCNM-ACBB1**

Barcode reader connection box for simplified wiring and integration
For use with ABR and TCNM barcode products

TCNM-ACMK-100

Barcode Memory Module; Provides backup and restore capability; Used with TCNM-ACBB1 connection box and ABR barcode reader



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America