

LED-4K-28D-O

28-INCH 4K MONITOR



Features :

- High resolution up to 3840x2160 display;
- Ultra-narrow bezel design, elegant appearance ;
- 178°H/178°V extra-wide viewing angle for overall viewing performance;
- High fidelity digital processing for a brilliant and vivid video;
- Support multiple signal interfaces including HDMI 2.0 x2, DP 1.2 x1, USB x1, Speaker x2;
- Support freesync, fluent image display;
- low blue light design, eye-protective.

Technical Specification

Model

Model	LED-4K-28D-O
-------	--------------

Display

Screen Size	28"
Aspect Ratio	16:9
Resolution	3840×2160 (UHD)
Backlight	LED
Brightness/Luminance	300 cd/㎡
Contrast	1000:1
Display Colour	1.073B
Viewing Angle(H/V)	178°(H)/178°(V)
Response time(typ.)	5ms
Refresh Rate	60Hz

Signals

Input	DP 1.2 ×1, HDMI 2.0 ×2,
Output	USB x1 (for charging)
Speaker	2W x2

General

Power Supply	AC 100-240V
--------------	-------------

Freesync	Yes	
Tilt	-5~15°	
Consumption (Standard)	40W	
Type	Internal	
Net Weight	7kg	
Gross Weight	8.8kg	
Wall Mount	75×75mm	
Dimension without standard (W×H×D)	637.88×368.53×57.36mm	
Package(W×H×D)	TBD	
Work Environment	Temperature	0 C~40 C (32°F~104°F)
	Humidity	10%~85%

Dimensions(mm)

