





Sturdy, robust, top of the range, domestic pressure washer for powerful outdoor cleaning

This sturdy and robust pressure washer satisfies all frequent and large cleaning tasks. It is built for durability with a long lasting induction motor and aluminium cylinder heads. It offers good ergonomics and a large range of operation with its 10m steel armed hose. It's perfect for those who want the toughest equipment with the very best performance. Ideal for cleaning horse trailers, boats, swimming pools as well as patio and garden furniture.

- 180 max pressure
- Metal pump with induction motor and alloy cylinder head for high durability.
- Handles all tasks on surfaces up to 60 m²/ hour.
- Excellent mobility on all types of surfaces with built-in trolley and large wheels.
- 10m superflex high-pressure hose.
- Convenient accessory storage in the machine.
- Easy storage of electric cable.
- Built-in detergent dosage-function and regulation.
- Long lance and telescopic handle supports good working positions.
- X-TRA model includes trolley and hose reel.

• Standard equipment

Included accessories		Ref. no.	Min. required	PREMIUM 180-10 UK
Hose and Connection				
	10M SUPERFLEX HOSE	128500082	0	•
Nozzle - High Pressure Washer				
	PREMIUM GENTLE NOZZLE	128501203	0	•
	PREMIUM ROUGH NOZZLE	128501202	0	•
Accessory				
	CLEANING TOOL BLACK	6520844	0	•
	G5 SPRAY HANDLE	128500072	0	•
	G5 SPRAY LANCE	128500075	0	•



Sturdy, robust, top of the range, domestic pressure washer for powerful outdoor cleaning

Model PREMIUM 180-10
UK

Ref. no. 128471148



PRODUCT FEATURES

Trolley	•
Detergent tank	•
Hose reel	•
Aluminium pump	•
Brass cylinder head	
Lance and spray gun storage	•
Storage of accessories	•
Cable storage	•
Pressure regulation	•
Gun with quick connection and swivel	•
Superflex (steel armed) hose	•
Automatic start/stop	•
Soft grip	•
Telescopic handle	•

Technical specifications PREMIUM 180-10
UK













Pump pressure (bar/MPa)	Max 180 / Max 18
Rated power (kW)	2.9
Voltage/phase/frequency/current (V~/Hz/A)	230 / 1~ / 50 / 12.6
Water flow Qmax/Qiec (l/h)	610 / 540
Cable length (m)	5
Hose length (m)	10
Max. inlet temperature (°C)	60
Length x width x height (cm)	39 x 38 x 95.5
Weight (kg)	26.8

• Standard equipment, ○ Supplementary accessories, □ Mountable equipment

Accessories		Ref. no.	Min. required	PREMIUM 180-10 UK
Accessory				
	CLEANING TOOL BLACK	6520844	0	•
	DRAIN AND TUBE 8M	128500461	0	○












Sturdy, robust, top of the range, domestic pressure washer for powerful outdoor cleaning

Accessories		Ref. no.	Min. required	PREMIUM 180-10 UK
	G5 SPRAY HANDLE	128500072	0	•
	G5 SPRAY LANCE	128500075	0	•
	INLET SUCTION HOSE 3M	128500673	0	○
	MULTI BRUSH	128470456	0	○
	NILFISK POWER PATIO	128500955	0	○
	NILFISK WATER FILTER	128500674	0	○
	ROOF CLEANER	128470040	0	○
	Under Chassis Spray Lance	6410763	0	○
	WALL HOOK	106411386	0	○
	Water Sand Blaster	6410758	0	○
Brush				
	CAR BRUSH HEAD	128500463	0	○
	GARDEN BRUSH HEAD	128470457	0	○



Sturdy, robust, top of the range, domestic pressure washer for powerful outdoor cleaning

Accessories		Ref. no.	Min. required	PREMIUM 180-10 UK
	RIM BRUSH HEAD	128470458	0	○
	Rotary Brush	126411395	0	○
	ROTARY BRUSH	6410762	0	○
	WASHING BRUSH	6410765	0	○
Hose and Connection				
	10M SUPERFLEX HOSE	128500082	0	●
	EXTENSION HOSE STEEL ARMED 7 M	6411048	0	○
	NILFISK BA VALVE COMP. GARDENA	106411177	0	○
Accessory Kit				
	MULTI BRUSH KIT	128470459	0	○
	O-RING KIT CONSUMER HPW	128500292	0	○
Nozzle - High Pressure Washer				
	PREMIUM GENTLE NOZZLE	128501203	0	●
	PREMIUM ROUGH NOZZLE	128501202	0	●