

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2152703605](#)  
**Status:** **Active**  
**Overview:** Temperature Sensor Cable Assemblies  
**Description:** Epoxy Coated NTC Thermistor Cables, 40.00mm Length, 3600 Beta Value, 10k# Resistance at 25°C with 1% Tolerance, Green

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                            |   |
|----------------------------|---|
| Product Family             | Cable Assemblies                                    |
| Series                     | <a href="#">215270</a>                              |
| Application                | Temperature Sensing                                 |
| Assembly Configuration     | Single Ended Connector                              |
| Beta Value (K)             | 3600  |
| Connector to Connector     | NTC Thermistor-to-Pigtail                           |
| Overview                   | <a href="#">Temperature Sensor Cable Assemblies</a> |
| Product Name               | NTC Temperature Sensor                              |
| Resistance Tolerance (%)   | 1   |
| Resistance at 25°C (kohms) | 10  |
| UPC                        | 195842044562  |


**Physical**

|                     |         |
|---------------------|---------|
| Cable Length        | 40.00mm |
| Circuits (Loaded)   | 1       |
| Color - Resin       | Green   |
| Gender              | N/A     |
| Lock to Mating Part | Yes     |
| Net Weight          | 0.150/g |
| Packaging Type      | Bag     |
| Single Ended        | Yes     |
| Wire Size AWG       | 28      |
| Wire/Cable Type     | N/A     |

**Material Info**

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 2152703605-000 |
|---------------|----------------|



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 15(a)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[215270 Series](#)