


BNC Crimp Plug



Specifications

Connector Type	: BNC Coaxial
Connector Body Style	: Straight Plug
Coaxial Termination	: Crimp
Impedance	: 50Ω
Coaxial Cable Types	: RG174
Contact Material	: Brass
Contact Plating	: Silver Plated Contacts
Frequency Max	: 11GHz
Connector Mounting	: Cable Mount

Diagram



No.	Description	Material	Finish
1	Insulation I	PTFE	None
2	Crimp Ferrule	Brass	Silver 70μ" Min.
3	Centre Contact		
4	Body		
5	Washer I	SK-5	Nickel 100μ" Min.
6	Spring Washer		
7	Washer II	Brass	
8	Gasket	Silicone	Red
9	Shell	Brass	Silver 70μ" Min.
10	Insulation II	PTFE	None

Part Number Table

Description	Part Number
BNC Coaxial, Straight Plug, Crimp, 50Ω, RG174, Brass	MP-13-55-1 TSS RG174U

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.