



Main

Product or component type	UPS network management cards
Provided equipment	CD with software User manual

Complementary

Range of product	Easy UPS 1Ph Management Accessory Cards & Management Software
Physical interface	1 Ethernet port 10/100BASE-T, transmission rate: 10/100 Mbit/s RJ45
Communication port protocol	TCP/IP SNMP v1 SNMP v2 SNMP v3 UDP (User Datagram Protocol)
Local signalling	LED (green) for port communication at 100 Mbps LED (yellow) for port communication at 10 Mbps
Mounting mode	-
Height	1.5 cm
Width	4.7 cm
Depth	2.3 cm
Net weight	0.11 kg

Environment

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Relative humidity	0...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.299 kg
Package 1 Height	4.191 cm
Package 1 width	16.789 cm

Package 1 Length	13.208 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	52
Package 2 Weight	20.6 kg
Package 2 Height	30 cm
Package 2 width	36 cm
Package 2 Length	61 cm

Contractual warranty

Warranty	1 year
----------	--------