



Main

Product or component type	UPS network management cards
Provided equipment	User manual

Complementary

Range of product	Easy UPS 1Ph Management Accessory Cards & Management Software
Physical interface	1 port RS232
Rated voltage	12 V DC
[In] rated current	200 mA
Output voltage	24 V DC 1 A for relay output
Mounting mode	-
Height	2.6 cm
Width	5.2 cm
Depth	8.4 cm
Net weight	0.05 kg

Environment

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Relative humidity	0...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.109 kg
Package 1 Height	4.801 cm
Package 1 width	16.612 cm
Package 1 Length	12.395 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	25

Package 2 Weight	54 kg
Package 2 Height	33 cm
Package 2 width	23 cm
Package 2 Length	48 cm

Contractual warranty

Warranty	1 year
----------	--------