

MT 18 LTX Compact (613021510) Cordless Multi-Tool
18V 2x2Ah Li-ion; Charger ASC 55 (220-240 V / 50 - 60 Hz); Plastic Carry Case

Order no. 613021510
EAN 4007430277534



Product may differ from Image



- Oscillating cordless multi-tool with high performance comparable to that of a mains powered version
- Indispensable for interior development such as cutting, sanding and scraping of different materials
- Tool holder for maximum compatibility to OIS, Starlock and other accessories
- Metabo Quick tool change system for time-saving, convenient change of accessories
- Quick work progress thanks to large oscillation angle and VTC-Electronics to maintain constant speed even under load
- Slim design and non-slip soft-grip surface for optimised handling
- Extra bright LED lights for good visibility of the working area
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Battery packs with capacity display for checking the charge status
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

Technical data

Characteristics

Type of battery pack	Li-ion
Battery voltage	18 V
Battery pack capacity	2 x 2 Ah
Orbital frequency with no load	7000 - 18000 rpm
Oscillation angle left/right	1.6 °
Bit retainer	Compatible with OIS and Starlock
Base plate, dimensions from corner to corner	93 mm / 3 5/8 "
Weight (including battery pack)	1.8 kg / 4 lbs

Vibration

Surface grinding	7.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Scraping	11.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Sawing with plunge cut saw blade	13 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Sawing with segmented sawing blade	11.6 m/s ²
Uncertainty of measurement K	3 m/s ²

Noise emission

Sound pressure level	77 dB(A)
Sound power level (LwA)	88 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Plunge saw blade 32 mm HCS (wood)
 Triangular hook and loop sanding plate 93 mm
 5 Hook and loop sanding sheets 93 mm P 80
 5 Hook and loop sanding sheets 93 mm P 120
 Suction Adapter
 Multi-adapter
 2 Li-Power battery packs (18 V/2.0 Ah)
 Charger ASC 55 "AIR COOLED"
 Plastic carry case
 Segment saw blade 85 mm BiM (wood + metal)
 Scraping knife, rigid 52 mm HCS