

10 ft Black USB 2.0 Extension Cable A to A - M/F

**Product ID:** USBEXTAA10BK



The USBEXTAA10BK 10-foot USB Extension Cable (A-A) features 1 USB A male connector and 1 USB A female connector, extending the connection between USB 2.0 devices by up to 10 feet - an ideal solution for better placement of peripheral devices, or adding flexibility to existing USB ports.

This high quality USB extension cable is fully rated for use with USB 1.1 and USB 2.0 devices, and is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

## Applications

- Extend your USB connection to connect a USB printer or any USB peripheral device to a PC or Mac at high-performance data transfer speed

## Features

- Designed and constructed to USB 2.0 specifications
- Molded strain relief
- Supports data transfer rates up to 480 Mbps

---

### Hardware

Warranty

Lifetime

Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Performance**

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

---

**Connector(s)**

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	USB Type-A (4 pin) USB 2.0

---

**Environmental**

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

---

**Physical Characteristics**

Color	Black
Wire Gauge	24/28 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	3.4 oz [96.0 g]

---

**Packaging Information**

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	3.6 oz [102.0 g]

---



**What's in the  
Box**

Included in Package      10 ft Black USB 2.0 Extension Cable A to A - M/F

---

***\*Product appearance and specifications are subject to change without notice.***

