



- » HOME
- » OVERVIEW
- » PRODUCTS
- » NEWS
- » WHERE TO BUY
- » CONTACT US
- » SUPPORT



Latest Products

PWI-AC90CBV2

90Watt Universal switching-mode power adapter for notebooks and LCDs



PWI-USB-HDV

Multi-Display USB 2.0 to DVI/VGA/HDMI adapter (up to 6 displays*)



PWI-DP-HDMI

Connect HDMI interface to a Display port interface



PWI-AC90SE

[SHOW LARGE PICTURE](#)

[Compatible Models](#)

PRODUCT FEATURES

Output Power (Max.)	90W
Overload Protection	Yes
Fanless	No noise
Short Circuit Protection	Yes
Line Regulation	±6%
Load Regulation	±6%
Switching Mode	Universal switching-mode power adapter for notebooks and LCDs
Special Connectors	15 Pieces Tip Connectors Including 7.4*5.0mm & 4.5*3.0mm with pin for Dell/HP, New USB Connector for Lenovo 4.8x1.7mm for HP, 3.0x1.0mm for tablet, 4.0x1.35mm for Asus. Dell Tip 4.5x30 (optional)
Efficiency	> 87% (TYP)
Unit Size	4.93"(W) x 2.25"(D) x 1.25"(H)
Net Weight	9 oz
Package Contents	Prudent way (PWI-AC90SE) 90W AC Netbooks. Laptops and LCDs Power Adapter 15 Tips Connectors User Manuals
Limited Warranty	One year
OUTPUT	
Output Voltage	12V 15V 16V 18V 19V 20V 24V DC12V-24V
Output Current	12V 15V 16V 18V 19V 20V @4.5Amp (max)
Output Current	24V @3.75Amp (max)
INPUT	
Input Voltage	AC120V AC230V
Vibration Input Voltage	AC100V-240V
Input Current	1.65AMP
Input Power	102VA
ENVIRONMENTAL	
Operating Temp.	0 to 40°C
Humidity	20% to 80%
RoHS Compliant	Yes



PWI-AC90LE



PWI-AC120LC



PWI-AC120LE



PWI-AD150HC



PWI-AC90CBV2



PWI-AC75NE

