

---

# Product datasheet

## ST 111 LONGLIFE

Starters for single operation at 230 V AC




## Product datasheet

### Technical data

#### Electrical data

Nominal voltage	220...240 V
Nominal wattage	65.00 W
Mains frequency	50...60 Hz

#### Dimensions & weight



Length	40.3 mm
Product weight	6.58 g
Diameter	21.5 mm

#### Additional product data

Product remark	Not suitable for L 70 W/Starters are available in two different designs, with identical technical features
Appropriate disposal acc. to WEEE	Yes

#### Capabilities

Dimmable	No
----------	----

#### Country specific categorizations

Order reference	ST 111
-----------------	--------

## Product datasheet

---

SINGLE CIRCUIT

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300270166	ST 111 LONGLIFE	Shipping carton box 1200 Pieces Unpacked	400 mm x 235 mm x 325 mm	30.55 dm <sup>3</sup>	8086.00 g
4050300854045	ST 111 LONGLIFE	Shipping carton box 400 Pieces Unpacked	227 mm x 179 mm x 227 mm	9.22 dm <sup>3</sup>	2748.83 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

OSRAM is distribution partner  
of LEDVANCE of LAMPS

**OSRAM**

OSRAM GmbH  
Marcel-Breuer-Strasse 6  
80807 Munich, Germany