

PRODUCT DATASHEET

CIR 100 160° 17 W/2700K E27

CIRCOLUX LED | Circular LED lamps with E27 screw base



AREAS OF APPLICATION

- LED alternative for applications requiring a high luminous flux
- General illumination
- Large shades and pendant luminaires
- Outdoor applications only in suitable luminaires
- LED alternative for applications requiring a high luminous flux

PRODUCT BENEFITS

- High luminous flux
- Long lifetime of up to 15,000 h
- Low energy consumption
- Three year guarantee

PRODUCT FEATURES

- Fold out base before first use
- Good quality of light; color rendering index $R_a: \geq 80$; constant chromaticity
- Not dimmable



TECHNICAL DATA

Electrical data

Rated wattage	17.00 W
Nominal wattage	17.00 W
Nominal voltage	220...240 V
Max. lamp no. on circuit break. 10 A (B)	30
Max. lamp no. on circuit break. 16 A (B)	50
Operating frequency	50/60 Hz
Power factor λ	> 0.50


Photometrical data

Nominal luminous flux	1521 lm
Rated luminous flux	1521 lm
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Luminous flux	1521 lm
Color rendering index Ra	≥ 80
Standard deviation of color matching	≤ 6 sdc _m
Rated color temperature	2700 K
Color rendering index Ra	≥ 80

Light technical data

Warm-up time (60 %)	< 0.50 s
Beam angle	160 °
Starting time	< 0.5 s

Dimensions & weight



Overall length	86.0 mm
-----------------------	---------

Diameter	260.0 mm
Outer bulb	T29
Length	86.0 mm

Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
Maximum temperature at tc test point	77.2 °C

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000
Lumen maintenance at end of service life	0.70

Additional product data

Base (standard designation)	E27
Mercury content	0.0 mg
Mercury-free	Yes
Show WEEE picto	Yes

Capabilities

Dimmable	No
-----------------	----

Certificates & standards

Energy efficiency class	A+
Energy consumption	17 kWh/1000h

Country-specific categorizations

Order reference	LED CIRCOLUX 17
------------------------	-----------------

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075271708	Folding carton box 1	42 mm x 263 mm x 292 mm	290.00 g	3.23 dm ³
4058075271715	Shipping carton box 4	278 mm x 272 mm x 184 mm	1632.00 g	13.91 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For further products and actual information concerning LED lamps see

▶ www.ledvance.com/ledlamps

For Guarantee see

▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.