

USB C Multiport Video Adapter w/ HDMI, VGA, Mini DisplayPort or DVI - USB Type C Monitor Adapter to HDMI 2.0 or mDP 1.2 (4K 60Hz) - VGA or DVI (1080p) - Space Gray Aluminum

Product ID: CDPVDHMDMP2G



This USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI or Mini DisplayPort (mDP) display.

Avoid the hassle of carrying different adapters, with a 4-in-1 USB-C monitor adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to any display using this multiport adapter.

The adapter features a magnetic retainer that guides the breakout cable into place for quick, secure portability. With a durable aluminum enclosure, the adapter can withstand being carried in your travel bag.

The HDMI and mDP outputs on this USB-C video adapter support UHD resolutions up to 4K 60Hz, while the VGA and DVI outputs support HD resolutions up to 1920 x 1200.

The USB-C adapter has a Space Gray housing and built-in USB-C cable designed to match your Space Gray MacBook, or MacBook Pro. The adapter is compatible with USB-C DP Alt Mode devices.

The adapter is also available with 4K 30Hz HDMI resolution support, in three colors: Space Gray (CDPVDHMDMP2G), Rose Gold (CDPVDHMDMPRG) and Silver (CDPVDHMDMP), so you can choose an adapter that matches your laptop or your color preference.

CDPVDHMDMP2G is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect to virtually any display while traveling

- Connect your MacBook to a provided VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your Space Gray MacBook

Features

- **4-IN-1 MULTIPORT USB-C VIDEO ADAPTER:** USB-C DP Alt Mode to any one of HDMI 2.0 (4K 60Hz & 7.1ch audio), mDP 1.2 (4K 60Hz & 2ch audio), VGA or DVI (1080p), HDCP 2.2/1.4, Thunderbolt 3 compatible
- **TOUGH & PORTABLE:** Durable aluminum space gray enclosure with a magnetically-secured hideaway cable wrap for on-the-go users in the office, at home, boardrooms, and classrooms
- **COMPATIBILITY:** USB-C display adapter for Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Laptop 3/Surface Book 3, TB3 MacBook Pro/Air, HP EliteBook/Spectre/ZBook, Chromebooks
- **TESTED & VERIFIED:** USB Type-C adapter tested @ 4K 60Hz mini DisplayPort/HDMI or 1080p VGA/DVI for compatibility w/ TV, monitor & projector brands like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson
- **EASY TO USE:** Supporting a driverless plug-and-play setup, this adapter is fully compatible with multiple OS platforms: Windows / macOS / Linux / Chrome OS

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
AV Output	HDMI - 1.4
	Mini DisplayPort - 1.2
	DVI-I (Digital Only) - Single-Link
	VGA
Chipset ID	Cypress - CYPD3120
	Parade - PS8348
	Parade - PS8617
	Parade - PS8338
	Parade - PS171
	Parade - PS176

Performance

Video Revision	HDMI 2.0
----------------	----------


DisplayPort 1.2

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920 x 1200 @ 60Hz
Maximum Digital Resolutions	4096 X 2160 @ 24Hz or 3840 X 2160 @ 60Hz (HDMI)
	4096 X 2160 @ 60Hz (mDP)
Supported Resolutions	Maximum HDMI output: 4096 X 2160 @ 24Hz or 3840 X 2160 @ 60Hz
	Maximum mDP output: 4096 X 2160 @ 60Hz
	Maximum DVI and VGA output: 1920 x 1200 @ 60Hz
	<i>Lower resolutions and refresh rates may also be supported</i>
Wide Screen Supported	Yes
Audio Specifications	HDMI - 7.1 Channel Audio
	DVI - No Audio Support
	VGA - No Audio Support
	Mini DisplayPort - 5.1 Channel Audio
MTBF	800,703 hours

Connector(s)

Connector A	USB-C (24 pin) DisplayPort Alt Mode
Connector B	Mini-DisplayPort (20 pin)
	VGA (15 pin, High Density D-Sub)
	DVI-I (29 pin)
	HDMI (19 pin)

Special Notes / Requirements



Note Only one video output is supported on the video adapter at a time, if multiple connections are made, only one of the outputs will function

Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	Storage: 5% ~ 90 % RH (no condensation) Operating: 10% ~ 85 % RH (no condensation)

Physical Characteristics

Color	Space Gray
Material	Aluminum
Cable Length	4.5 in [11.5 cm]
Product Length	6.9 in [17.5 cm]
Product Width	5.6 in [14.2 cm]
Product Height	1.2 in [30 mm]
Weight of Product	6.5 oz [185 g]

Packaging Information

Package Length	2.2 in [55 mm]
Package Width	4.1 in [10.5 cm]
Package Height	0.6 in [16 mm]
Shipping (Package) Weight	4.3 oz [121 g]

What's in the Box

Included in Package	travel A/V adapter
---------------------	--------------------

**Product appearance and specifications are subject to change without notice.*