

# WorkForce WF-2810DWF



## DATASHEET / BROCHURE



Compact 4-in-1 inkjet printer designed for homes and small offices, with Wi-Fi and mobile printing.

This 4-in-1 inkjet printer with Wi-Fi is stylish, compact and easy-to-use in your home office. Reduce waste and costs with A4 double-sided printing and affordable individual inks. Printing with devices on the go is easy with Wi-Fi Direct and mobile printing apps.

### Compact and stylish

With its sleek and refined form, it's easy to integrate this space-saving, 4-in-1 model into any home office.

### Easy to use

The printer's functions can be easily navigated on the spot thanks to the intuitive user interface and LCD screen. Save paper and money with A4 double-sided printing.

### Affordable solution


Epson's four-colour 603 inks provide reliable, vibrant and clear prints with minimal outlay. Each colour is supplied individually, so you only replace the colours you need. This makes individual inks 50% more efficient compared to tri-colour cartridges<sup>1</sup>. Reduce costs even further with Epson's XL cartridges, that can print 2.5x more pages<sup>2</sup>.

### Go wireless

Use Wi-Fi for printing and scanning wirelessly around the home, and Wi-Fi Direct for printing without a wireless network. With Wi-Fi Direct you can send documents to print from smart devices using the Epson iPrint<sup>3</sup> app. It can even receive files from almost anywhere in the world via Epson Email Print<sup>3</sup>.

## KEY FEATURES

- **Wi-Fi 4-in-1**  
Print, scan, copy and fax
- **Business features**  
Business-quality documents and A4 double-sided printing
- **Easy mobile printing**  
Print easily from your smartphone or tablet<sup>3</sup>
- **Individual inks**  
Save money by only replacing the colour used
- **3.7cm LCD screen**  
Easily navigate through the printer's functions



## LOGISTICS INFORMATION

SKU	C11CH90401
EAN code	8715946665955
Country of Origin	Indonesia
Layer	4 Units
Layer Block	6 Units

## WorkForce WF-2810DWF

### WHAT'S IN THE BOX

- Main unit
- Individual Ink Cartridges
- Software (CD)
- Warranty document
- Power cable
- Setup guide

### INK CARTRIDGE COMPATIBILITY



### INK YIELD DATA

	Starfish 603	Starfish 603XL
●	150 pages*	500 pages*
● ● ●	130 pages*	350 pages*

\* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

For more information please contact:

Home users: 0343 90 37766  
Business users\*: 0871 42 37766  
Republic of Ireland: 01 436 7742  
Or visit us at <https://www.epson.co.uk/contactus>  
\* 10p per minute plus network extras.

Web: [www.epson.co.uk](http://www.epson.co.uk)  
[www.epson.ie](http://www.epson.ie)

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.  
Product information is subject to change without prior notice.  
Last extracted: 2020-04-30

1. Based on testing carried out by BLI in July 2019, compared to equivalent competitor (HP and Canon) printer models, using tri-colour cartridges, according to the manufacturers' websites, July 2018. Weighting for Document and Photo printing applied based on TNS 'Printing Usage & Attitudes Study', June 2013.
  2. For more information, please visit [www.epson.eu/pageyield](http://www.epson.eu/pageyield)
  3. Epson iPrint and Epson Creative Print require a wireless connection and the Epson printing apps. Epson Email print and Epson Remote Print Driver require an internet connection. For more information, supported languages and devices, please visit [www.epsonconnect.eu](http://www.epsonconnect.eu)
1. Based on testing carried out by BLI in July 2019, compared to equivalent competitor (HP and Canon) printer models, using tri-colour cartridges, according to the manufacturers' websites, July 2018. Weighting for Document and Photo printing applied based on TNS 'Printing Usage & Attitudes Study', June 2013.

**EPSON**<sup>®</sup>