



## 50" 4K UHD Digital TV with Separate Wireless Headphones

- Two or more people can watch the TV simultaneously at different volume settings
- Headphones included with separate independent volume control
- 30 metre range from headphones to TV
- Audio USB for headphone dongle
- No sound or lip sync delay from TV speakers to headphones
- Up to three TVs can be used close together (3 headphone channels allow easy switching)
- Headphones can select different TVs to watch in real time during listening
- No limit to the number of headphones that can be used with one TV
- Remote control mutes everything
- Built-in Freeview T2 HD and Digital Freeview Channels
- HDMI input for your external devices and consoles
- Can be wall mounted (400mm x 400mm)

EAN		5060750401163
Specifications	Model No.	C5020HH4K
	Chipset	3683
	Sales Market	UK
	VESA Size	400 x 400
	Wall Mount Screws	M6 x 10
	Speaker Output	2 x 8w
	Actual Size of Display (Diagonal)	50"

Display	Display Type	LED
	Resolution	3840 x 2160
	Brightness (nit)	200
	Contrast	4000:1
	Display Colours	1.07G colour
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178
	Response Time	9.5ms

Terminals	HDMI Input	3
		480i, 480p, 586i, 576p, 720p, 1080i, 1080p, 4k
		(CEC, ARC)
	USB	2
	EARPHONE	1
	RCA Component + AUDIO Input	1
	RCA Composite + AUDIO Input	1
	Optical Digital AUDIO Output	1
	RF Input	1

Accessories	Remote	1
	Battery	AAA x 2
	User Manual	English

Other Features	DVD Player	No
	DVB-S	Without
	DVB-S2	Without
	DVB-T	With
	DVB-T2	With
	CI	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/ Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift
		EPG recording reservation

Power	Power Supply	AC 100-240V ~50Hz/60Hz
	Operation Power Consumption	90W
	Max Power Consumption	120W
	KWh/annum	132kWh
	Standby Consumption	<0.5W
	Energy Efficiency Class	A

Dimensions	Unit Dimension With Stand	1130 x 265 x 723mm
	Unit Dimension Without Stand	1130 x 91 x 660mm
	Weight (Kg)	10.6