



18V ROTARY HAMMER SDS+ 24MM

DHR242RTJ

DHR242 models are 24mm (15/16") Cordless Combination Hammers powered by 18V Li-ion Battery



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-Ion
Voltage	18 v
Battery Quantity (5.0ah)	2
Capacity in Concrete	24 mm
Capacity in Steel	13 mm
Capacity in Wood	27 mm
Optimum Drilling Range	4 - 16 mm
Impact energy	2.0 J
Blows per minute	0 - 4700 bpm
No Load Speed	0 - 950 rpm
Vibration: Drilling	3.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Vibration: Hammer Drilling	13.5 m/sec ²
Vibration: Chiselling	10.5 m/sec ²
Net weight	3.3 kg

USER BENEFITS

- Able to drill in concrete as fast or faster than 24V Cordless Combination Hammer model BHR200.
- One touch slide chuck for SDS-plus bit.
- Easy-to-grip handle ergonomically designed to: • give maximum power thrust. • provide a sure and comfortable grip in any operation; overhead application, drilling with palm-up or palm-down grip.
- 3 mode operation • Rotation + Hammering • Hammering only • Rotation only
- The tool body is seperated into the upper and lower housings at the foot of handle portion where the houses are jointed with vibration absorbing cushion rubbers.
- Higher productivity than model BHR202 achieved by using efficient Brushless DC motor to reduce energy loss by 30%
- Unique rubber joint construction suppresses the transmission of vibration to battery terminals, minimizing battery failures such as terminal breakage or poor electrical contact.

[Link to product - makitauk.com](https://www.makita.com)



RELATED PRODUCTS

(Recom

STANDARD ACCESSORIES

197282-4

Battery BL1850B 18v Li-ion



821552-6

MAKPAC CONNECTOR CASE (TYPE



837649-1

INNER TRAY



DC18RC

DC18RC COMPACT CHARGER



OTHER