

## TECHNICAL DATA SHEET

Part#: 38-SE

Hemostats - 6" 30°Curved - SS  
Ideal for clamping parts for inspection

The 38-SE stainless steel locking hemostat with 30°curved serrated jaws is clean room safe. The overall length is 6".

• Precision Level	★★
• Material	SS (AISI 440)
• Surface Resistivity	Conductive
• Shape	Curved
• Tip Size	
• Tip Angle	30°
• Tip Length	
• Body Width	0.283" (7.08mm)
• Body Height	0.182" (4.55mm)
• OAL	6" (150mm)
• Weight (OZ)	2
• UPC	662847003905
• Schedule B	9018.90.80.00
• ECCN	EAR99
• UNSPSC Code	42151685
• Country of Origin	Pakistan
• Group	Curved

