

TECHNICAL DATA SHEET

Part#: 37-SE

Hemostats - 6" Straight - SS
Ideal for clamping parts for inspection

The 37-SE stainless steel locking hemostat with straight serrated jaws is clean room safe. The overall length is 6".

• Precision Level	★★
• Material	SS (AISI 440)
• Surface Resistivity	Conductive
• Shape	Straight
• Tip Size	
• Tip Angle	Straight
• Tip Length	
• Body Width	0.269" (6.73mm)
• Body Height	0.172" (4.3mm)
• OAL	6" (150mm)
• Weight (OZ)	2
• UPC	662847003868
• Schedule B	9018.90.80.00
• ECCN	EAR99
• UNSPSC Code	42151685
• Country of Origin	Pakistan
• Group	Straight

