

## TECHNICAL DATA SHEET

Part#: 39PH

Hemostats - 8" Straight - SS - Vinyl-Coated Handle  
Ideal for clamping parts for inspection

The 39PH stainless steel locking hemostat with straight serrated jaws has vinyl-coated handles. The overall length is 8".

• Precision Level	★★
• Material	SS (AISI 440)
• Surface Resistivity	Insulative
• Shape	Straight
• Tip Size	
• Tip Angle	Straight
• Tip Length	
• Body Width	0.283" (7.08mm)
• Body Height	0.231" (5.78mm)
• OAL	8" (200mm)
• Weight (OZ)	2
• UPC	662847010705
• Schedule B	9018.90.80.00
• ECCN	EAR99
• UNSPSC Code	42151685
• Country of Origin	Pakistan
• Group	Straight - Vinyl Handles

