

# VOLTAGE/CONTINUITY TESTERS

## MEASURE/INDICATE AC/DC VOLTAGE



- Two new Voltage/Continuity Testers for 2021
- CE, UKCA and cULus or UL Listed (all models)
- CAT IV 600V, CAT III 1000V and CAT III 600V options
- Digital Display Multifunction and Voltage level display
- IP42 Dustproof/Water (61-557 & 61-547)
- 2 Meter drop protection (61-557 & 61-547)
- Lead holders are spaced to test tamper resistant outlets
- Bright LED torch, continuity, NCVT, GFCI\* test, LoZ (61-557)



### 61-557

Voltage & Continuity Tester  
w/LCD, GFCI\*, Torch & NCVT  
CAT IV 600V



### 61-547

8 Range AC/DC Voltage Indicator  
w/Polarity Indicator  
CAT III 600V



### 61-090EU

Vol-Con® Elite Digital Voltage Tester  
w/NCVT, LoZ and GS38 compliant test leads  
CAT III 1000V



**NCV** — Torch

**NCV, Continuity, High Voltage, Visual Indications, Augment Audible Indications**

**Backlit Display**

**GFCI Test**  
(\*only applicable to the US market)

**LoZ**  
Eliminates ghost voltage (induced voltage from adjacent conductors)

**Uses Standard Test Leads (included)**

**Probe Holder for Storage/Measurement**  
(61-557, 61-547)

**Universal Magnetic Strap Clip**  
(61-557, 61-547)

**Universal Magnetic Strap Clip**  
(UMHS-757)  
allows for two-handed operation of probes with tester suspended from strap (61-557 & 61-547) (sold separately)

# VOLTAGE/CONTINUITY TESTERS AND VOLTAGE TESTERS

<b>VOLTAGE TESTER SELECTION GUIDE</b> <b>FOUR NEW NCVTS FOR 2021</b>	 <b>NEW</b>	 <b>NEW</b>	
	<b>61-557</b>	<b>61-547</b>	<b>61-090EU</b>
<b>FEATURES</b>			
CAT Rating (Safety)	CAT IV 600V	CAT III 600V	CAT III 1000V
Listing Preferred	cULus, CE, UKCA	cULus, CE, UKCA	UL, CE, UKCA
Drop Protection	6.6 ft. (2m)	6.6 ft. (2m)	—
Ingress Protection	IP42	IP42	—
AC Voltage (Volts)	6 ~ 600	24 ~ 600	24 ~ 600
DC Voltage (Volts)	6 ~ 600	12 ~ 600	6 ~ 220
High Voltage Alarm	ACV >36 or DCV >50V	ACV/DCV >48V	—
Audible Continuity	✓	—	✓
Visual Continuity	✓	—	LED
Backlight	✓	—	—
Low Impedance (LoZ)	✓	—	✓
NCV	90-600V AC	—	40-600V AC
Auto Ranging	✓	—	✓
Magnetic Strap Mount	✓	✓	—
Test Probe Holder	✓	✓	—
Torch	✓	—	—
Auto-Power Off (APO)	✓	—	—
Low Battery Indicator	✓	—	✓
Battery Type (included)	3 x 1.5V AAA	—	4 x 1.5V AAA
LCD Display Count	600	—	—
Backlight	✓	—	—
DC Polarity Indication	✓	✓	—
Leads	Removable	Fixed	Removable
GFCI** Test	✓	—	—
Display	LCD	Neon Lamps	LED
Warranty	2 Year*	2 Year*	2 Year*
<b>ACCESSORIES</b>			
Test Leads (included)	TL-757	—	TL-102EU
Magnetic Hanging Strap (sold separately)	UMHS-757	UMHS-757	—

\* Go to [idealind.com](http://idealind.com) for complete warranty information

\*\* only applicable to the US market

Specifications are subject to change without notice.




Scan this QR code with your smartphone to learn more about the testers.



**Probe Holders** are spaced to test tamper resistant outlets (61-557 & 61-547)



**Continuity Testing** (61-557)



**Backlit Display and Torch** (61-557)



**NCVT** in tip detects presence of AC voltage (61-557)



**Tests GFCI\*\*** protected circuits (61-557)



**LoZ** option to eliminate ghost voltage (61-557)



IDEAL INDUSTRIES, INC.

IDEAL INDUSTRIES EMEA

Unit 3, Europa Court, Europa Boulevard, Warrington, WA5 7TN, UK | +44 (0)1925 444 446 | [eur.sales@idealindustries.com](mailto:eur.sales@idealindustries.com)

International offices:

Australia • Canada • China • India • Germany • Mexico • Middle East • UK

For complete sales office contact information, visit us at:

[www.idealind.com](http://www.idealind.com)

Form No. P-6045-EMEA  
©2021 IDEAL INDUSTRIES, INC.

05/21  
Printed in UK