

GENTIX Corded Optical Mouse



Models may vary from the image shown

Professional quality and a modern design at an amazing price

GENTIX - a mouse to hold on to!
Modern design, accurate scroll wheel action and precise mouse key pressure points make this product unique in its price class. The solid rubber sides make the mouse comfortable to use and ensure smooth, accurate cursor control even in hectic situations. The GENTIX mouse can be connected quickly and easily to any Notebook, PC or Mac via the 1.8-metre cable with USB connection.

Key benefits

- Reliable corded mouse with three buttons and optical sensor
- Rubber side surfaces and rubber scroll wheel offer improved grip
- Symmetrical design - suitable for left and right-handed users
- High-resolution optical sensor with 1000 dpi resolution for precise and flowing cursor control
- Plug & Play for easy start up
- 1.8 m cable with USB connection for use on the laptop and PC

Technical Data:

Weight (product):

120 g

Total weight (with packaging):

164 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-15°C to 60°C

Operating Temperature:

0°C to 40°C

Current Consumption:

max. 100 mA

Interface:

- USB

Product approvals:

- VDE GS
- c-tick
- CE
- FCC
- cTUVus



System requirements:

- USB connection

Delivery Volume:

- GENTIX Corded Optical Mouse
- Operating instructions in hard copy

Dimensions (product):

111.5 x 68.5 x 35 mm

Packaging dimensions:

139 x 95 x 45 mm

Packaging (version):

White box

Reliability:

- Standard keys: >3 mill. operations

Mouse:

- Scanning: Optical
- Resolution: 1000 dpi
- Number of Keys: 3
- Mouse wheel design: Scroll wheel with key function
- Design: Symmetrical
- Connection: USB
- Housing colour: Product dependant, see table "Models"
- Key colour: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 40
- Number of master packages per pallet: 21

Warranty:

3-year limited manufacturer's guarantee
For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the

product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Mouse Housing colour	Mouse Key colour
1	GENTIX Corded Optical Mouse	JM-0300-0	4025112082740	pale grey	pale grey
2	GENTIX Corded Optical Mouse	JM-0300-2	4025112074295	black	black