

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Screwdriver

Bosch GO



The Bosch GO Cordless Screwdriver – Minimum Effort,
Maximum Efficiency

The most important data

Battery voltage	3.6 V
Max. screw diameter	5 mm
Weight excl. battery	0.31 kg

Part Number 0 601 9H2 170[> More product information](#)

Technical data

Technical data

Torque (soft/hard/max.)	2.5/5/- Nm
No-load speed (1st gear / 2nd gear)	- 360 rpm
Battery type	Lithium-ion
Chuck capacity, min./max.	6.35 mm
Battery voltage	3.6 V
Weight excl. battery	0.31 kg
Packaging dimensions (width x length x height)	162 x 280 x 90 mm
Drill chuck, version	1/4" with internal hexagon shank
Battery capacity	1.5 Ah
Weight incl. battery	0.31 kg

'Total vibration values (Screwdriving)'

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Screw diameter

Max. screw diameter	5 mm
---------------------	------

Noise/vibration information

Screwdriving

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- Dual-activation mode – simply push machine forward or press 'on' button to begin
- Mechanical clutch – select from 5 torque settings up to 'maximum performance mode'
- Easy-to-control – tool stops immediately after deactivation via an electronic brake

