

**BOSCH**

Invented for life

# Product data sheet

## Power tools for trade & industry

Cordless Random Orbit Sander

### GEX 12V-125



Compact random orbit sander for always-on-the-go professionals

#### The most important data

Sanding pad diameter	125 mm
Orbit diameter	2.5 mm
No-load speed	6,000 – 10,000 rpm

**Part Number** 0 601 372 100[> More product information](#)

## Technical data

### Technical data

Sanding pad diameter	125 mm
No-load speed	6,000 – 10,000 rpm
Orbital stroke rate	12,000 – 20,000 opm
Eccentricity	1.25 mm
Sanding sheet / disc attachment	Hook-and-loop fastening
Weight excl. battery	0.8 kg
Tool dimensions (width)	153 mm
Tool dimensions (length)	194 mm
Tool dimensions (height)	108 mm
Orbit diameter	2.5 mm
Packaging dimensions (width x length x height)	442 x 357 x 151 mm
Battery voltage	12 V

### 'Total vibration values (Sanding solid wood)'

Vibration emission value ah	2.2 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

## Noise/vibration information

### Sanding solid wood

Vibration emission value ah	2.2 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



# Product data sheet

Power tools for trade & industry

## Advantages:

- Outstanding balance close to the workpiece and supreme ergonomics of palm rest and grip ensure optimal tool control
- Lean and compact design makes sanding in tight spaces easy
- Easy operation thanks to intuitive operating concept

