



Product data sheet

Power tools for trade & industry

Cordless Multi-Cutter

GOP 18V-28



The versatile power performer in the Bosch StarlockPlus category

The most important data

| | |
|-------------------------------------|--------------------|
| Battery voltage | 18 V |
| No-load rotation | 8,000 – 20,000 opm |
| Oscillation angle on left and right | 1.4 ° |

Part Number 0 601 8B6 001[> More product information](#)

Technical data

Technical data

| | |
|--|--------------------|
| Battery voltage | 18 V |
| No-load rotation | 8,000 – 20,000 opm |
| Oscillation angle on left and right | 1.4 ° |
| Packaging dimensions (width x length x height) | 360 x 440 x 155 mm |
| Weight incl. battery | 1.6 kg |

'Total vibration values (Grinding)'

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 3.4 m/s ² |
| Uncertainty K | 1.5 m/s ² |

'Total vibration values (Sawing with plunge-cutting saw blade)'

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 8 m/s ² |
| Uncertainty K | 1.5 m/s ² |

'Total vibration values (Sawing with segment saw blade)'

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 5.7 m/s ² |
| Uncertainty K | 1.5 m/s ² |

Noise/vibration information

Grinding

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 3.4 m/s ² |
| Uncertainty K | 1.5 m/s ² |

Sawing with plunge-cutting saw blade

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 8 m/s ² |
| Uncertainty K | 1.5 m/s ² |

Sawing with segment saw blade

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 5.7 m/s ² |
| Uncertainty K | 1.5 m/s ² |

Scraping

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 8.6 m/s ² |
| Uncertainty K | 1.5 m/s ² |



Product data sheet

Power tools for trade & industry

Advantages:

- Superior Starlock interface of optimised 3-dimensional tight connection for highest direct power transfer
- LED spot illuminates workspaces, improving work visibility even in the dark
- Snap-in function enables fast and easy tool accessory change

