

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Random Orbit Sander

GEX 18V-125



Optimal control for sanding larger surfaces

The most important data

Sanding pad diameter	125 mm
Orbit diameter	2.5 mm
No-load speed	6,000 – 10,000 rpm

Part Number 0 601 372 200[> More product information](#)

Technical data

Technical data

Sanding pad diameter	125 mm
No-load speed	6,000 – 10,000 rpm
Orbital stroke rate	12,000 – 20,000 opm
Eccentricity	1.25 mm
Sanding sheet / disc attachment	Hook-and-loop fastening
Weight excl. battery	1.1 kg
Tool dimensions (width)	153 mm
Tool dimensions (length)	224 mm
Tool dimensions (height)	108 mm
Orbit diameter	2.5 mm
Packaging dimensions (width x length x height)	442 x 357 x 151 mm
Battery voltage	18 V
Weight incl. battery	1.6 kg

'Total vibration values (Sanding solid wood)'

Vibration emission value ah	1.9 m/s ²
Uncertainty K	1.5 m/s ²

Noise/vibration information

Sanding solid wood

Vibration emission value ah	1.9 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Outstanding balance close to the workpiece and supreme ergonomics of palm rest and grip offer optimal tool control
- Brushless motor and Bosch's Professional 18V system ensure fast work progress and high endurance
- Easy and intuitive operation

